

## Recommended CEREC settings for VOCO's Grandio blocs

	Primemill	MC X	MC XL	MC X5 (laboratoy)
General	Blocks up to 70mm and universal mount No disc Built-in scanner for QR code (manual entering of product possible)	Blocks up to 55mm and universal mount No disc	Blocks up to 85mm and universal mount No disc	All block sizes with Universal mount Also disc with universal mount 98mm
Grandio blocs	Cerasmart 270 (size 12 and 14L*)	Cerasmart 270 (size 12 and 14L*)	Cerasmart 270 (size 12 and 14L*)	Cerasmart 270 (size 12 and 14L*)

VOCO's Grandio blocs are compatible with the CEREC Milling machine when used with the settings indicated above.



\*Depending on the crown design, the software may default to a 14 block and has to be manually changed back to a 14L to work